

MGA4005UW Series

CSA Z7396.1 Premium Medical Air Control Panel

Specifications

- UL 508A listed control panel
- NEMA 12 rated enclosure
- Compliance with CSA Z7396.1
- Molded case circuit breaker disconnects for each motor with through the door lockable mechanism
- Dual 120V control circuit transformer with fused primary and secondary circuit with dedicated separate circuit breaker for each compressor and control
- Pressure switch connection for backup system operation should primary control circuit fail*
- Lighted H-O-A switches and magnetic starters with three legs thermal overload for each compressor
- 7" multicolor touch screen LCD monitor displays operating status, compressor run hours, faults, system pressure, alarms and service alert for each compressor, dryer control, dryer pressure switch, CO and dew point
- Full system schematic and manual viewable via HMI
- High temperature shutdown for each compressor
- PLC controller with control logic to start the lag compressor automatically if the lead compressor fails to operate. Logic also automatically removes failed or switched off compressor from duty sequence.
- All components used in control panel are non-proprietary and can be replaced using standard off the shelf components**
- Able to accept any range of sensors complying to 24VDC 4-20mA standard on site without the use of factory programming
- Web server features includes email and/or text notification in case of alarm and live remote monitoring of system operation status via device ethernet IP-address***
- Alarm logging and performance trend on HMI with ability to email for viewing from other devices***
- Normally open and normally closed dry contact for remote monitoring of CSA Z7396.1 alarm points



Optional Features

- Building automation communication gateway with BacNet® TCP/IP protocol
- 65 KAIC SCCR rating
- Amperage readout for each motor
- Ambient temperature monitoring
- Factory remote connection via secure gateway (with enable/disable switch operated by local personnel)
- Backup pressure switch factory mounted and wired for single point connection to air receiver

*Pressure switches sold separately

** Programable parts will require Axecon downloaded program

*** Internet access required on site for this feature to operate

Website: www.3dproto.ca

Email: sales@3dproto.ca